

CURVEX 3 BASIC OVEN LOGGER CX3005, CX3010

PRODUCT DESCRIPTION

The CurveX 3 Basic is an oven recorder designed for daily use in powder coating lines.

CurveX 3 Basic a 4-channel temperature data logger is built in a sturdy machined aluminium case that fulfils the basic needs for quality control in powder coating applications. Its ease of use and affordable price level makes it the ideal job-coaters instrument.



TQC Sheen has a wide range of interchangeable probes and heat barriers available that allow the CurveX 3 Basic to be used over the whole temperature range. All CurveX insulation boxes and CurveX probes, and the single heat absorber / bracket can be used with the CurveX 3 Basic. (See accessory list)

FEATURES

- · Operate through only 3 large buttons
- Meaningful feedback of multi coloured LED's
- Factory calibrated for immediate use
- Downloads data through a standard USB port
- Rechargeable battery pack through USB connector
- Large memory of max. 160.000 readings
- Memory for 10 different batches, automatically overwrites the oldest results
- Programmable "paint type" memory for immediate "pass / fail" result
- Flat design, only 16 mm, for use in low clearance ovens
- · Compatible with Ideal Finish Analysis software

SCOPE OF SUPPLY

CX3005 CurveX 3 Basic Data Logger comes with:

- CX3004 CurveX 3 Basic datalogger
- CM1105 USB Cable
- GL0103 USB Memory Stick with Ideal Finish Analysis software
- CX5010 Ideal Finish Analysis License Key
- CL0018 Factory calibrated, calibration certificate included
- CX3059 Small protective case

CX3010 CurveX 3 Basic Data Logger Kit comes with

- CX3004 CurveX 3 Basic datalogger
- CM1105 USB Cable
- GL0103 USB Memory Stick with Ideal Finish Analysis software
- CX5010 Ideal Finish Analysis License Key
- CL0018 Factory calibrated, calibration certificate included
- CX2005 Insulationbox
- CX3050 Insulation box logger bracket
 - CX3060 Plastic Carrying Case



ORDERING INFORMATION

CX3005 CurveX 3 Basic Oven Logger
CX3010 CurveX 3 Basic Oven Logger Kit

SPECIFICATIONS

CurveX 3 Basic logger

Measuring range $0 \,^{\circ}\text{C}$ to $500 \,^{\circ}\text{C}$ / $32 \,^{\circ}\text{F}$ to $932 \,^{\circ}\text{F}$ Operating temperature: $0 \,^{\circ}\text{C}$ to $60 \,^{\circ}\text{C}$ / $32 \,^{\circ}\text{F}$ to $140 \,^{\circ}\text{F}$

Accuracy $\pm 1 \,^{\circ}\text{C} / 1.8 \,^{\circ}\text{F}$

Channels 4

Sample interval time 1 s to 60 min

Memory 10 batches with 16000, or 1 batch with 160000 readings

Display Three multi-colour LED's

Interface USB

Housing material Anodised Aluminium

Dimensions (D x W x H) 100 x 85 x 16 mm / 3.94 x 3.35 x 0.63 inch

Power supply Rechargeable battery

Battery life time* 1200 hour continuous use, 27 years in stand-by

Weight 190 g / 6.7 oz.

TQC Sheen Ideal Finish Analysis software

Supported Operating Systems Windows Vista, Windows 7 and Windows 8 / 8.1

Platform 32 b or 64 b Memory 32 MB Required Hard Disk space 128 MB

USE

The CurveX 3 Basic is placed in an insulated box before it passes through the oven. The instrument measures and registers the temperature at several places of the work piece. The preset paint type specification is evaluated against the temperature over time resulting in a clear cure pass or fail. The measurements are uploaded to a PC via the oven temperature data logger's USB port and analysed using the Ideal Finish software program.

SPECIAL CARE

- Though robust in design, this instrument is precision-machined. Never drop it or knock it over.
- Always clean the instrument after use.
- Clean the instrument using a soft dry cloth. Never clean the instrument by any mechanical means such as a wire brush or abrasive paper. This may cause, just like the use of aggressive cleaning agents, permanent damage.
- Do not use compressed air to clean the instrument.

TQC Sheen 2908 LL Capelle aan den IJssel phone: +31 (0)10-7900100 email: info@tqcsheen.com Molenbaan 19 The Netherlands fax: +31 (0)10-7900129 www.tqcsheen.com

^{*}After 300 cycles charge from 0 to 100% the battery will retain a capacity of 80%. In general such battery need replacement after approx. 2 years continuous use.



- Always keep the instrument in its case when not in use.
- We recommend annual calibration.

Batteries in carry-on baggage (aircraft cabin)


The battery employed in our CurveX 3 Basic is a generic single cell Lithium-Ion battery, 3.7V 1400mAh. The battery employed in the CurveX 3 Basic has a capacity of 5.18 Watt-hours, and is rated for low-power use only. A protection circuitry has been applied to the CurveX 3 Basic mainboard as per best practice.

Based on US DOT regulations (49 CFR, Sec. 175.10), the CurveX 3 Basic battery satisfies all demands, most notably:

- The battery is non-replaceable for the end user and therefore does not classify as 'spare'
- The battery is rated below 100 Watt-hours per battery
- The battery is protected from damage and short circuit

The battery is assembled into an end product and classified to be freely transported on aircraft both in carry-on and check-in luggage. When carried-on, please keep the provided product documentation with the device in order to be able to provide regulatory agencies relevant information about your device when requested.

TEST CONDITIONS FOR USE WITHOUT HEAT ABSORBER




Tested in combination with the Insulation Box CX2005 and Insulation Box Logger Bracket CX3050 with a start temperature of 20°C (68°F). (So without heat absorber)

phone: +31 (0)10-7900100

+31 (0)10-7900129





Tested with the **insulation box CX2005** in combination with the **energy absorber CX2011** (a high density energy-collecting media) with a start temperature of 20°C (68°F).

ACCESSORIES

Air temperatur Art. No Application		Probe Mounting	Cable Type	Cable Length	Max Temperature	
CX2020	Air	Spring clamp	Coiled polyurethane	1500 mm / 59,06 inch	300°C / 572°F	
CX2021	Air	Spring clamp	Coiled polyurethane	3000 mm / 118,11 inch	300°C / 572°F	
CX2022	Air	Spring clamp	Coiled polyurethane	5000 mm / 196,85 inch	300°C / 572°F	
CX2026	Air	Spring clamp	Coiled polyurethane	10500 mm / 34,45 ft	300°C / 572°F	
CX2023	Air	Spring clamp	Stainless steel braided lead	1500 mm / 59,06 inch	480°C / 896°F	
CX2024	Air	Spring clamp	Stainless steel braided lead	3000 mm / 118,11 inch	480°C / 896°F	
CX2069	Air	Magnet	Coiled polyurethane	1500 mm / 59,06 inch	300°C / 572°F	
CX2068	Air	Magnet `	Coiled polyurethane	3000 mm / 118,11 inch	300°C / 572°F	
CX2073	Air	Magnet	Coiled polyurethane	5000 mm / 196,85 inch	300°C / 572°F	
			probes for CurveX			
Art. No	Application	Probe Mounting	Cable Type	Cable Length	Max Temperature	
CX2030	Surface	Spring clamp	Coiled polyurethane sheath	1500 mm / 59,06 inch	300°C / 572°F	
CX2040	Surface	Spring clamp	Coiled polyurethane	3000 mm / 118,11 inch	300°C / 572°F	
CX2041	Surface	Spring clamp	Coiled polyurethane	5000 mm / 196,85 inch	300°C / 572°F	
CX2045	Surface	Spring clamp	Coiled polyurethane	10500 mm / 34,45 ft	300°C / 572°F	
CX2046	Surface	Vice clamp	Coiled polyurethane	10500 mm / 34,45 ft	300°C / 572°F	
CX2048	Surface	Spring clamp	Stainless steel braided lead	1500 mm / 59,06 inch	480°C / 896°F	
CX2049	Surface	Spring clamp	Stainless steel braided lead	3000 mm / 118,11 inch	480°C / 896°F	
CX2050	Surface	Magnet	Coiled polyurethane	1500 mm / 59,06 inch	300°C / 572°F	
TQC She		908 LL Capelle he Netherlands		e: +31 (0)10-7900100 +31 (0)10-7900129	email: info@tqcsheen.com www.tqcsheen.com	



CX2060	Surface	Magnet	Coiled polyuret	thane	3000 mm / 118,11 inc	ch	300°C / 572°F
CX2062	Surface	Magnet	Coiled polyuret	thane	5000 mm / 196,85 inc	ch	300°C / 572°F
CX2061	Air	Magnet	Coiled polyuret	thane	10500 mm / 34,45 ft		300°C / 572°F
CX2055	Surface	Magnet	Stainless steel	braided lead	1500 mm / 59,06 inch		480°C / 896°F
CX2056	Surface	Magnet	Stainless steel	braided lead	3000 mm / 118,11 inc	ch	480°C / 896°F
CX2065	Universal	Ring	Coiled polyuret	thane	1500 mm / 59,06 inch	ı	300°C / 572°F
CX2066	Universal	Ring	Coiled polyuret	Coiled polyurethane		ch	300°C / 572°F
CX2072	Universal	Ring	Coiled polyuret	thane	5000 mm / 196,85 inc	ch	300°C / 572°F
CX2085	Universal	Ring	Stainless steel	braided lead	1500 mm / 59,06 inch	ı	480°C / 896°F
CX2086	Universal	Ring	Stainless steel	braided lead	3000 mm / 118,11 inc	ch	480°C / 896°F
CX2090	Universal	Ring	Inconel tube		1500 mm / 59,06 inch	ı	1000°C / 1832°F
CX2091	Universal	Ring	Inconel tube		3000 mm / 118,11 inc	ch	1000°C / 1832°F
CX2092	Universal	Ring	Inconel tube		5000 mm / 196,85 inc	ch	1000°C / 1832°F
CX2063	Air/Surface	Wire	Coiled polyuret	thane	1500 mm / 59,06 inch	ı	300°C / 572°F
CX2064	Air/Surface	Wire	Coiled polyuret	thane	3000 mm / 118,11 inch		300°C / 572°F
CX2067	Air/Surface	Wire	Coiled polyuret	Coiled polyurethane		ch	300°C / 572°F
CX2087	Air/Surface	Wire	Stainless steel	braided lead	1500 mm / 59,06 inch		480°C / 896°F
CX2088	Air/Surface	Wire	ire Stainless steel braide		3000 mm / 118,11 inch		480°C / 896°F
CX2093	Air/Surface	Wire	Inconel tube		1500 mm / 59,06 inch		1000°C / 1832°F
CX2094	Air/Surface	Wire	Inconel tube		3000 mm / 118,11 inc	ch	1000°C / 1832°F
			obes for Curv	reX			
Art. No	Application	Probe	Cable Type		Cable Length		Max
CX2097	Air	Mounting Spring clamp	Stainlass staal	hraidad laad	1500 mm / 59,06 inch	,	Temperature 480°C / 896°F
CX2097	Air	Spring clamp		Stainless steel braided lead		•	
CAZU90	ΛII	Spring claimp	Stainless steel braided lead 5000 mm / 196,85 inch		CII	480°C / 896°F	
Infra-r	ed surface	temperatu	re probes for	CurveX			
Art. No	Application	Probe	Cable Type		Cable Length		Max
		Mounting					Temperature 480°C / 896°F
CX2095	Surface	Spring clamp		Stainless steel braided lead		1500 mm / 59,06 inch 1500 mm / 59,06 inch	
CX2096	Surface	Magnet		Stainless steel braided lead			480°C / 896°F
CX2099	Surface	Magnet	Stainless steel	braided lead	5000 mm / 196,85 inc	ch	480°C / 896°F
Standa	ard insulat	ion boxes f	or CurveX				
		Dimensions	Dimensions	Approximate	Heat Sink	Max	
	Depth		Height	Weight		-	erature
CX2004	240 mm /	105 mm /	50 mm /	1600 g /	included	300°C	/ 572°F
	9,45 inch	4,13 inch	1,97 inch	3,53 lbs			
CX2009	240 mm /	105 mm /	60 mm /	1700 g /	included	300°C	/ 572°F

3,75 lbs

2650 g/

5,85 lbs

4200 g/

9,26 lbs

* to be ordered s	separately
-------------------	------------

9,45 inch

10,04 inch

10,04 inch

CX2003 255 mm /

CX2005 255 mm/

4,13 inch

225 mm / 7

8,86 inch

225 mm /

8,86 inch

2,36 inch

2,76 inch

140 mm /

5,51 inch

0 mm /

CX2014*

CX2011*

300°C / 572°F

300°C / 572°F



Absolute silicone free insulation boxes for CurveX

Art. No	Dimensions Depth	Dimensions Width	Dimensions Height	Approximate Weight	Heat Sink	Max Temperature
CX2300	240 mm /	225 mm/	140 mm /	4200 g	CX2011*	180°C / 356°F
	9,45 inch	8,86 inch	5,51 inch	9,26 lbs		
CX2017	240 mm /	225 mm /	140 mm /	4200 g	CX2011*	500°C / 932°F
	9,45 inch	8,86 inch	5,51 inch	9,26 lbs		
CX2002	280 mm /	230 mm /	180 mm /	8000 g /	CX2011*	500°C / 932°F
	11,02 inch	9,06 inch	7,09 inch	17,64 lbs	CX2012 *	

^{*} to be ordered separately

Other Accessories

CX2013 Heat sink LDPE Add-on module for insulation box CX2002, CX2017 and 2005

CX2014 Heat sink U-shaped for insulation box CX2003

CX2011 Heat sink LDPE for insulation box CX2002, CX2017 and CX2005

CX2012 Extra heat sink for insulation box CX2002

CX3050 Insulation box logger bracket

CX2100 CurveX Basic probe identification kit (1-6)

CM1105 USB Cable

CX2077 Ideal Finish Analysis Software on CD with printed manual in box

SAFETY PRECAUTIONS

- Do not exceed the specified time at temperature limits in order to protect the equipment.
- Maintenance and inspection should be carried out at the correct intervals
- Operating personnel should be informed before starting with maintenance or repair work
- Do not open the instrument. In case of malfunction always consult the manufacturer. Not suitable to be put in the sun or in the high light

DISCLAIMER

The right of technical modifications is reserved.

The information given in this sheet is not intended to be exhaustive and any person using the product for any purpose other than that specifically recommended in this sheet without first obtaining written confirmation from us as to the suitability of the product for the intended purpose does so at his own risk. Whilst we endeavour to ensure that all advice we give about the product (whether in this sheet or otherwise) is correct we have no control over either the quality or condition of the product or the many factors affecting the use and application of the product. Therefore, unless we specifically agree in writing to do so, we do not accept any liability whatsoever or howsoever arising for the performance of the product or for any loss or damage (other than death or personal injury resulting from our negligence) arising out of the use of the product. The information contained in this sheet is liable to modification from time to time in the light of experience and our policy of continuous product development.